

WORKHORSE™ Professional Grade

High Purity 222 o-ring seal cartridge housing

FEATURES:

The distribution loop, direct feed or recirculation, should always be protected by final filtration after the storage tank, distribution pump possible UV or DI. This removes 99% of bacteria and endotoxin as well as protects equipment from resin breakthrough.

Filter housings are wall mounted or skid mounted for space saving. Non-corrosive design includes fiberglass, virgin polypropylene, PVC 80, and 304 stainless steel. Housings are fitted with 222 o-ring sanitary seals for single open-end cartridges. Sample ports are included for pre/post filtration testing.



8822
Shown

SPECIFICATIONS				
Model	Inlet/Outlet	Cartridge Size In. (L)	Maximum Flow GPM	Dimensions In. (W x D x L)
Single Housing				
8821	¾" SOC or THRD	20	10	15" x 6" x 29"
Dual Housing				
8822	1 ¼" SOC or THRD	20	20	15" x 15" x 38"
Triple Housing				
8823	1 ½" SOC or THRD	20	30	15" x 20" x 38"

* The cartridge filter utilized in the housing may influence the maximum flow rate.



NuStream™
filtration